Zero in on a potential radioactive source quickly and more effectively with an RC2^{PLUS}

- Improved sensitivity and greater response
- Easy to use
- Larger high definition display with multiple languages
- Lightweight with longer battery life
- RC2^{PLUS} is available in two versions; Basic with Total Count version or the Advanced ROI Analysis version
- RadView software for integration



RC2PLUS

HANDHELD RADIATION DETECTION SYSTEM

Durable and Dependable

The Basic RC2^{PLUS} automatically sets an alarm threshold over the total background count rate average upon each startup. This allows the RC2PLUS to detect very low radiation levels even when hidden by shielding such as scrap metal, waste, or other dense material. The RC2^{PLUS} utilizes a large internal, high grade PVT scintillator to maximize sensitivity.

The Advanced RC2^{PLUS} utilizes both a PVT scintillator and a Geiger-Mueller tube to perform "Region Of Interest" (ROI) Analysis which allows the operator to see the distributed gamma energies in a histogram form. Once the ROI ranges are selected, a specific alarm threshold can be set for each ROI. This unique technology dramatically increases sensitivity while decreasing the adverse effects of "noise" caused by ambient background radiation. The RC2^{PLUS} provides many additional features such as Does Rate Alarm, Data Storage, and Graph Plotting.

Upgradable for Increased Flexibility

At any time the RC2^{PLUS} Basic can be easily upgraded to the RC2^{PLUS} Advanced. The RC2^{PLUS} Advanced stores operator results in a histogram record which can be downloaded via USB to RadComm's exclusive RadView software for further analysis. All reports can be saved in PDF format and archived for future reference. Remote servicing/diagnostics and potential future software updates of the RC2^{PLUS} can be achieved via an internet or network connection with RadComm's software application.

Upgradable for Radon Detection

New technology for express analyzing (< 5min) Radon concentration in air by using low energy resolution PVT plastic scintillator and high energy resolution Lanthanum Bromide inorganic scintillator as the gamma-detectors.

Size

- Detector Dimensions:
 5.9" H(15cm) x 8.5" L(21cm) x 4" W(10cm)
- System weight: 3.4lbs (1.5kg)
- Detector case: Durable plastic with protective silicone sleeve

Electronics

- · Integral PMT with EM shielding
- Audio & visual alarm with vibration
- Stable low noise, high voltage power supply
- Battery: Internal Lithium Ion with charge indicator
- Battery Life: up to 20 hours
- Battery Recharge Time:
 - Wall charger: 2.5 hrs
 - PC USB: 6 hrs (estimated)

Environmental

- Operating Temperature: -20°C (-4°F) to +60°C (140°F)
- Shock resistance: Complies with ANSI N42.34

Display

- Backlit RGB colour LCD 320x240 resolution
- Viewing area: 3.5"(8.9cm) TFT LCD
- Basic: selectable units of measure: (CPS, uSv/h, uR/r)
- Advanced: Histogram graph

Software for Advanced

- Menu driven user interface
- Configurable data storage with backup
- E-mail capability (with network connection)

Detector Specifications

- Basic & Advanced utilizes PVT:
- Size 4"(101.6mm) x 3"(76.2mm) x 2"(50.8mm)
- Advanced also includes: Geiger-Mueller tube, size 0.59"(12mm) x 1.9"(45mm), for high dose rate

Response/Sensitivity

- Energy Range: 30 KeV 2.0 MeV
- Gamma histogram: 256 Channels, channel capacity 16 bits

RC2^{PLUS} Basic vs Advanced Each RC2^{PLUS} Package Includes:

- RC2^{PLUS} instrument charged and ready for use
- Hard shell carrying case
- Smart battery wall charger
- USB key with operation manual embedded
- Calibration certificate

| Feature | Basic Option | Advanced Option |
|------------------------------|-----------------|--------------------|
| Search+Find | ✓ | ✓ |
| Total Counts | ✓ | ✓ |
| Dose Rate | ✓ | ✓ |
| Dose Rate Alarm | | ✓ |
| Histogram | | ✓ |
| Graph Plotting | | ✓ |
| ROI Analysis | | ✓ |
| ROI Alarm Threshold Settings | | ✓ |
| Date Storage | | ✓ |
| Accumulated Dose | | ✓ |

RC2PLUS - Docking Station (Optional)

- Docking Station charges RC2^{PLUS} instrument
- Provides area monitoring while the RC2^{PLUS} is docked
- Audio and visual alarm with reset button
- Wall mounted with security lock









164, St-Jean-Baptiste Mercier, QC J6R 2C2 450-691-9090 info@ande.ca

ONTARIO

275, Sheldon Drive, Unit 3 Cambridge, ON N1T 1A3 519-894-9069 nadams@gnde.ca ALBERTA

7307, 50 street NW Edmonton, AB T6B 2J9 587-689-6811 Ifields@gnde.ca

www.qnde.ca

1-800-361-3630