

Next Level in Radiation Detection

- Industry leading technology
- Fast reacting alarm response with isotopic identification
- Utilizes gamma spectra energy deconvolution technique
- State of the art large volume, high resolution Thallium Doped Sodium Iodide crystal (NaI(Tl)) scintillation detectors
- Standalone technology or combined with PVT based systems
- Flexible installation allowing for use in a variety of applications and industrial settings
- Stabilization without a radioactive check source
- Neutron detection capability (Optional)

RC7000

NEUSPEC SPECTROSCOPIC RADIATION DETECTION SYSTEMS

Next Level in Radiation Detection

The RC7000 utilizes gamma spectra energy deconvolution techniques, a significant improvement over conventional PVT scintillator based systems. This technology is specifically designed to enhance a radiation detection systems ability to recognize specific Gamma energies which can adversely affect alarm thresholds. The RC7000 utilizes a series of advanced isotopic identification algorithms in conjunction with RadComm's industry-leading and proven Region Of Interest (R.O.I.) analyses to provide best in class detection and identification.

Stabilization Without a Radioactive Check Source

RC7000 systems incorporate large sodium iodide thallium doped crystals (NaI(Tl)) specifically selected for high resolution signal response. The crystals are protected inside a stainless steel case with a low density aluminum door. To ensure the best possible spectral analyses, the sodium iodide crystals must be continuously stabilized. The RC7000 stabilizes these crystals with specific Gamma energies associated with the ambient background energies, thus eliminating the need for a radioactive check source.

Flexible Multiple Applications

The RC7000 can be used in a variety of applications including: enhancement of an existing PVT based vehicle monitoring system, conveyor belt and area monitoring. RC7000's gamma spectra energy deconvolution algorithms give the system the ability to either ignore (for example NORM or medical isotopes) or alarm on specific gamma energies.



DISTRIBUÉ PAR / DISTRIBUTED BY

QND
QUALITY NDE LTD

QUEBEC

166, St-Jean-Baptiste
Montréal, QC H3R 2C2
450-881-9000
info@qnde.ca

ONTARIO

275, Sheldon Drive, Unit 3
Cambridge, ON N1T 1A3
519-894-9000
radarma@qnde.ca

ALBERTA

7307, 50 street NW
Edmonton, AB T6B 2J9
587-688-8811
flexco@qnde.ca

www.qnde.ca

1-800-361-3630

RC7000 Series Components

- Detector assemblies
- RadLink embedded controller
- Smart Infrared presence sensors
- Large touchscreen monitor
- Remote communications package (Optional)

RadLink Controller Features

- Large touchscreen LCD monitor
- Large storage capacity for system operational information and alarms
- Easy to follow multilingual menu outlines and descriptions
- Multi-level security password control
- Detailed alarm and scan data storage
- Easy to set alarm configuration menu
- Network access for remote service and monitoring
- Radiation levels displaying in either: CPS, R/h, Sv/h
- Vehicle speed measurement in Km/h or mph
- Internal operating temperature displayed in Celsius & Fahrenheit
- Adjustable audio alarm
- Counter for number of scans in a 24 hour period for incoming and outgoing scans
- Detailed alarm information displayed and stored after every alarm
- Configurable email reporting
- Various string outputs available

Detector Features

- Detector case: 36"H(915cm)x 24"L(60cm)x 6"W(15cm)
- Outer detector case: painted aluminum
- NEMA 4 (IP65) rated
- Integral PMTs with EM shielding
- High speed DSP circuitry with High SNR
- Ultra stable high voltage software adjustable
- Temperature sensor
- Internal operating temperature: -20°C (-4°F) +55°C (131°F)
- Relative humidity: 93% non-condensing at 40°C (104°F)
- Vibration: 2 g for 15 min at 10 – 33 Hz in XYZ directions (ANSI N42.34, ANSI N42.38)
- Shock: Complies with ANSI N42.34, ANSI N42.38
- EM compatibility: ANSI N42.34, ANSI 42.38 compliant
- CE compliant (EU safety, RFI and EMI directives)

Spectrometer Specifications

- NaI(Tl) Crystal - Variety of sizes available
- Energy Resolution 8.0% or better for 662 KeV
- Energy Range: 20 KeV to 3.0 MeV (Gamma)
- System Calibration Software Monitor with Operator Alert
- Dose Rate Range 1nSv/h to 1.0mSv/h Auto-Ranging
- Gamma Spectrum - 512 Channels, channel capacity 16 bits
- Correction - non-linear energy calibration
- Detection Specification: Meets ANSI N42.38 (2006)

Options


- Camera
- External alarms
- Supervisory software
- Neutron detection (He3 or alternative)




Cobalt-60 Spectra



Thorium-232 Spectra



Cesium-137 Spectra



Barium-133 Spectra



DISTRIBUE PAR / DISTRIBUTED BY:

QND
QUALITY NDE LTD

QUEBEC

194, St-Jean-Baptiste
Mercier, QC J6R 2C2
450-891-0690
info@qnde.ca

ONTARIO

275, Sheldon Drive, Unit 3
Cambridge, ON N1T 1A3
519-894-8069
radams@qnde.ca

ALBERTA

7307, 50 street NW
Edmonton, AB T6B 2J9
587-488-8211
ifields@qnde.ca

www.qnde.ca 1-800-361-3630