

# Tabletop Ultrasonic Cleaner

R30 is ideal for cleaning a wide variety of lab/dental/medical/hospital instruments and mechanical parts, engine and electrical components, jewelry and other items.

## Features

**1. High Definition Industrial Level LCD**  
Press "ultrasound" to start cleaning process.

**2. One Button Start**

User-friendly LCD display allows user to monitor working status and set parameters.

**3. 24 Hours Non-Stop Running**

Different from the common tabletop ultrasonic cleaner, R30 can work 24 hours continuously.

**4. Timing**

0-60min. or continuously running adjustable.

**5. Heating**

30-80°C adjustable by user.

**6. Ultrasonic Power Adjustable**

10-100% adjustable linearly to fit to different workpiece demands.

**7. Ultrasonic Frequency Adjustable**


Two frequencies are switchable easily for workpiece coarse cleaning and fine cleaning, also very suitable for applications with many different workpiece. Low frequency applied for common workpiece and high frequency for delicate workpiece.

**8. Power Supply**

R30 is very flexible in power supply. Optional power supply 110V/220V, 50Hz/60Hz.

**9. Plug**

Different plugs to fit to your local need, like European Standard Plug, USA Plug, Malaysia Plug, Italy Plug And Switzerland Plug etc.



## \* Technical Specification \*

Max. Volume: 30L

Ultrasonic Power: 600Watts

Protection Class: IP21

Drainage: 1/2"

Working Environment Temperature: 0-40°C

G. Weight: 44kgs

Overall Size (LxWxH): 670x375x410mm

Inner Tank Size (LxWxH): 550x300x180mm

Basket Size (LxWxH): 520x270x120mm

Power Supply: 110/220V, 50/60Hz, 1 Phase

Packing Size (LxWxH): 750x450x590mm

Max. Loading Capacity: 15KG

Heating Power: 900W

Ultrasonic Frequency:

Single Frequency (28kHz, 40kHz, 80kHz etc) or  
Dual-Frequency (25/45kHz, 28/68kHz, 40/80kHz,  
40/130kHz, 80/130kHz)

DISTRIBUTED BY/DISTRIBUÉ PAR:



**QUEBEC:**

164, St-Jean-Baptiste  
Mercier, QC J6R 2C2  
Tel: 450-691-9090  
info@qn.de.ca

[www.qn.de.ca](http://www.qn.de.ca)

**ONTARIO:**

275, Sheldon Drive, Unit 3  
Cambridge, ON N1T 1A3  
Tel: 519-894-9069  
nadams@qn.de.ca

**1-800-361-3630**

**ALBERTA:**

7307, 50 street NW  
Edmonton, AB T6B 2J9  
Tel: 587-689-6811  
admin.west@qn.de.ca

